


* 1-4 (Strang / Colonne montante / Montante)

X (Entfernen Sie J1 / Retirez le J1 / Rimuovi J1)

Info: Verdrillte kabel verwenden / Utiliser des câbles torsadés

Utilizzare cavi twistati Art.336904 - Eldas 101 282 009


21 INT 1.2/00



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
 Retirez le J1
 Rimuovi J1


Art.346020
 Eldas 964 930 490



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
 Retirez le J1
 Rimuovi J1


Art.346020
 Eldas 964 930 490



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
 Retirez le J1
 Rimuovi J1


Art.346020
 Eldas 964 930 490



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
 Retirez le J1
 Rimuovi J1

Art.346020
 Eldas 964 930 490



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
 Retirez le J1
 Rimuovi J1

Art.346020
 Eldas 964 930 490

21 TAB 1.1/00


* 1-4 (Strang / Colonne montante / Montante)

X (Entfernen Sie J1 / Retirez le J1 / Rimuovi J1)

Info: Verdrillte kabel verwenden / Utiliser des câbles torsadés

Utilizzare cavi twistati Art.336904 - Eldas 101 282 009


21 INT 1.3/00



**Entfernen Sie J1
 Retirez le J1
 Rimuovi J1**

Art.346020


Eldas 964 930 490



**Entfernen Sie J1
 Retirez le J1
 Rimuovi J1**

Art.346020


Eldas 964 930 490



**Entfernen Sie J1
 Retirez le J1
 Rimuovi J1**

Art.346020

Eldas 964 930 490



**Entfernen Sie J1
 Retirez le J1
 Rimuovi J1**

Art.346020


Eldas 964 930 490



**Entfernen Sie J1
 Retirez le J1
 Rimuovi J1**

Art.346020

Eldas 964 930 490



**Entfernen Sie J1
 Retirez le J1
 Rimuovi J1**

Art.346020


Eldas 964 930 490

21 INT 1.1/00

* 1-4 (Strang / Colonne montante / Montante)
 X (Entfernen Sie J1 / Retirez le J1 / Rimuovi J1)

Info: Verdrillte kabel verwenden / Utiliser des câbles torsadés
 Utilizzare cavi twistati Art.336904 - Eldas 101 282 009

21 INT 1.4/00



Eldas 964 752 209 - 964 752 289

Art.344642 - 344643




Etagen-Taster
 Poussoir d'étage
 Chiamata al piano

Entfernen Sie J1
 Retirez le J1
 Rimuovi J1

Art.346020

Eldas 964 930 490




Eldas 964 752 209 - 964 752 289

Art.344642 - 344643



Art.346020

Eldas 964 930 490




Eldas 964 752 209 - 964 752 289

Art.344642 - 344643



Art.346020

Eldas 964 930 490




Eldas 964 752 209 - 964 752 289

Art.344642 - 344643



Art.346020

Eldas 964 930 490




Eldas 964 752 209 - 964 752 289

Art.344642 - 344643



Art.346020

Eldas 964 930 490



Eldas 964 752 209 - 964 752 289

Art.344642 - 344643



Art.346020

Eldas 964 930 490


21 INT 1.2/00

* 1-4 (Strang / Colonne montante / Montante)

X (Entfernen Sie J1 / Retirez le J1 / Rimuovi J1)

Info: Verdrillte kabel verwenden / Utiliser des câbles torsadés
 Utilizzare cavi twistati Art.336904 - Eldas 101 282 009


21 INT 1.5/00



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
Retirez le J1
Rimuovi J1


Art.346020
 Eldas 964 930 490



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
Retirez le J1
Rimuovi J1


Art.346020
 Eldas 964 930 490



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
Retirez le J1
Rimuovi J1


Art.346020
 Eldas 964 930 490



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**

Entfernen Sie J1
Retirez le J1
Rimuovi J1

Art.346020
 Eldas 964 930 490



Eldas 964 752 209 - 964 752 289 **Art.344642 - 344643**





Entfernen Sie J1
Retirez le J1
Rimuovi J1

Art.346020
 Eldas 964 930 490

21 INT 1.3/00

* 1-4 (Strang / Colonne montante / Montante)
X (Entfernen Sie J1 / Retirez le J1 / Rimuovi J1)

Info: Verdrillte kabel verwenden / Utiliser des câbles torsadés
 Utilizzare cavi twistati Art.336904 - Eldas 101 282 009



*1
 21 INT 1.4/00