





Chemin de câbles

Table transversale



Breite (mm) Oberfläche	Chemin de câbles CF 30			Chemin de câbles CF 54			Chemin de câbles CF 80			Chemin de câbles CF 105			Chemin de câbles CF 150			Chemin de câbles HDF 105			Chemin de câbles FCFA 54			Largeur (mm) Surface
																						
	L : 3000 mm			L : 3000 mm			L : 3000 mm			L : 3000 mm			L : 3000 mm			L : 3000 mm			L : 3000 mm			
50	PG	-		CM000060	-		-		-		-		-		-		-		CM082060	PG	50	
100	PG	-		CM000070	-		-		-		-		-		-		-		CM082070	PG	100	
150	PG	-		CM000080	-		-		-		-		-		-		-		CM082080	PG	150	
200	PG	-		CM000090	-		-		-		-		-		-		-		CM082090	PG	200	
300	PG	-		CM000100	-		-		-		-		-		-		-		CM082100	PG	300	
400	PG	-		-	-		-		-		-		-		-		-		CM082200	PG	400	
450	PG	-		CM000250	-		-		-		-		-		-		-		CM082250	PG	450	
500	PG	-		-	-		-		-		-		-		-		-		CM082300	PG	500	
600	PG	-		-	-		-		-		-		-		-		-		CM082400	PG	600	
50	EZ	CM000011		CM000061	-		-		-		-		-		-		-		CM082061	EZ	50	
100	EZ	CM000021		CM000071	-		CM800101		CM000891		-		-		-		-		CM082071	EZ	100	
150	EZ	CM000031		CM000081	-		-		CM000901		-		-		-		-		CM082081	EZ	150	
200	EZ	CM000041		CM000091	-		CM800201		CM000911		CM000951		-		-		-		CM082091	EZ	200	
300	EZ	CM000051		CM000101	-		CM800301		CM000921		CM000961		-		-		-		CM082101	EZ	300	
400	EZ	CM000801		CM000201	-		CM800401		CM000931		CM000971		-		-		-		CM082201	EZ	400	
450	EZ	CM000831		CM000251	-		-		CM001931		CM001011		-		-		-		CM082251	EZ	450	
500	EZ	CM000811		CM000301	-		CM800501		CM000941		CM001021		-		-		-		CM082301	EZ	500	
600	EZ	CM000851		CM000401	-		-		CM001031		-		-		-		-		CM082401	EZ	600	
50	GC	CM000013	CM000016 ⁽¹⁾	ZnAl	CM000063	CM000066 ⁽¹⁾	ZnAl	-	-		-		-		-		-		-	GC	50	
100	GC	CM000023	CM000026 ⁽¹⁾	ZnAl	CM000073	CM000076 ⁽¹⁾	ZnAl	CM800103	CM000893	CM000896 ⁽¹⁾	ZnAl	-	CM450623		-		-		-	GC	100	
150	GC	CM000033	CM000036 ⁽¹⁾	ZnAl	CM000083	CM000086 ⁽¹⁾	ZnAl	-	CM000903	CM000906 ⁽¹⁾	ZnAl	-	CM450633		-		-		-	GC	150	
200	GC	CM000043	CM000046 ⁽¹⁾	ZnAl	CM000093	CM000096 ⁽¹⁾	ZnAl	CM800203	CM000913	CM000916 ⁽¹⁾	ZnAl	CM000953	CM450643		-		-		-	GC	200	
300	GC	CM000053	CM000056 ⁽¹⁾	ZnAl	CM000103	CM000106 ⁽¹⁾	ZnAl	CM800303	CM000923	CM000926 ⁽¹⁾	ZnAl	CM000963	CM450663		-		-		-	GC	300	
400	GC	-	CM000806 ⁽¹⁾	ZnAl	CM000203	CM000206 ⁽¹⁾	ZnAl	CM800403	CM000933	CM000936 ⁽¹⁾	ZnAl	CM000973	CM450683		-		-		-	GC	400	
450	GC	-	CM000836 ⁽¹⁾	ZnAl	CM000253	CM000256 ⁽¹⁾	ZnAl	-	CM001936 ⁽¹⁾	ZnAl	CM001013	CM450693		-		-		-	-	GC	450	
500	GC	-	CM000816 ⁽¹⁾	ZnAl	CM000303	CM000306 ⁽¹⁾	ZnAl	CM800503	CM000943	CM000946 ⁽¹⁾	ZnAl	CM001023	CM450703		-		-		-	GC	500	
600	GC	-	CM000856 ⁽¹⁾	ZnAl	CM000403	CM000406 ⁽¹⁾	ZnAl	-	CM001033	CM001036 ⁽¹⁾	ZnAl	-	CM450723		-		-		-	GC	600	
50	304L	CM000018		CM000068	-		-		-		-		-		-		-		-	304L	50	
100	304L	CM000028		CM000078	-		-		CM000898		-		-		-		-		-	304L	100	
150	304L	CM000038		CM000088	-		-		CM000908		-		-		-		-		-	304L	150	
200	304L	CM000048		CM000098	-		-		CM000918		-		-		-		-		-	304L	200	
300	304L	CM000058		CM000108	-		-		CM000928		-		-		-		-		-	304L	300	
400	304L	-		CM000208	-		-		CM000938		-		-		-		-		-	304L	400	
450	304L	-		-	-		-		-		-		-		-		-		-	304L	450	
500	304L	-		CM000308	-		-		CM000948		-		-		-		-		-	304L	500	
600	304L	-		CM000408	-		-		CM001038		-		-		-		-		-	304L	600	
50	316L	CM000014		CM000064	-		-		-		-		-		-		-		-	316L	50	
100	316L	CM000024		CM000074	-		-		CM000894		-		CM450624		-		-		-	316L	100	
150	316L	CM000034		CM000084	-		-		CM000904		-		CM450634		-		-		-	316L	150	
200	316L	CM000044		CM000094	-		-		CM000914		-		CM450644		-		-		-	316L	200	
300	316L	CM000054		CM000104	-		-		CM000924		-		CM450664		-		-		-	316L	300	
400	316L	-		CM000204	-		-		CM000934		-		CM450684		-		-		-	316L	400	
450	316L	-		-	-		-		-		-		CM450694		-		-		-	316L	450	
500	316L	-		CM000304	-		-		CM000944		-		CM450704		-		-		-	316L	500	
600	316L	-		CM000404	-		-		CM001034		-		CM450724		-		-		-	316L	600	







(1) = Auf Anfrage

(1) = Auf Anfrage

Chemin de câbles

Table transversale



Largeur (mm) Surface	Couvercle CP		Toiture CPD		Chemin de câbles CFC 50		Chemin de câbles CFG 50		Chemin de câbles TXF 35			Couvercle CP 35		Chemin de câbles G-Mini 50		Chemin de câbles ZF31 50		Chemin de câbles ZF31 25		Chemin de câbles TRI HDF 80		Largeur (mm) Surface
																				 Stützabstand bis 6 m		
	L : 2000 mm		L : 2000 mm		L : 3000 mm		L : 3000 mm		L : 3000 mm			L : 3000 mm		L : 3000 mm		L : 3000 mm		L : 3000 mm		L : 3000 mm		
35	EZ	-	GS	-	-	-	-	-	CM755001	-	CM755100	-	CM430111	-	-	-	-	-	-	-	EZ	35
50	EZ	CM646010	GS	-	-	-	-	-	-	-	-	-	-	-	CM348010	-	CM348000	-	-	-	EZ	50
100	EZ	CM646020	GS	-	-	-	CM003221	-	-	-	-	-	-	-	-	-	-	-	-	-	EZ	100
150	EZ	CM646030	GS	-	-	-	CM003231	-	-	-	-	-	-	-	-	-	-	-	-	-	EZ	150
200	EZ	CM646040	GS	-	-	-	CM003241	-	-	-	-	-	-	-	-	-	-	-	-	-	EZ	200
300	EZ	CM646050	GS	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	EZ	300
400	EZ	CM646060	GS	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	EZ	400
450	EZ	CM646090	GS	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	EZ	450
500	EZ	CM646070	GS	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	EZ	500
600	EZ	CM646080	GS	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	EZ	600
35	GC	-	-	-	-	-	-	-	CM755003	-	CM755103	-	-	-	-	-	-	-	-	-	GC	35
50	GC	CM646013	CM350664 ⁽¹⁾	ZnMg	-	CM004063	-	-	-	-	-	-	-	-	CM348160	-	CM348150	-	-	-	GC	50
100	GC	CM646023	CM350665 ⁽¹⁾	ZnMg	-	CM004073	CM003223	-	-	-	-	-	-	-	-	-	-	CM001116 ⁽¹⁾	ZnAl	-	GC	100
150	GC	CM646033	CM350666 ⁽¹⁾	ZnMg	-	-	CM003233	-	-	-	-	-	-	-	-	-	-	-	-	-	GC	150
200	GC	CM646043	CM350667 ⁽¹⁾	ZnMg	-	CM004093	CM003243	-	-	-	-	-	-	-	-	-	-	-	-	-	GC	200
300	GC	CM646053	CM350668 ⁽¹⁾	ZnMg	-	CM004103	-	-	-	-	-	-	-	-	-	-	-	-	-	-	GC	300
400	GC	CM646063	CM350669 ⁽¹⁾	ZnMg	-	CM004203	-	-	-	-	-	-	-	-	-	-	-	-	-	-	GC	400
450	GC	CM646093	CM350670 ⁽¹⁾	ZnMg	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	GC	450
500	GC	CM646073	CM350671 ⁽¹⁾	ZnMg	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	GC	500
600	GC	CM646083	CM350672 ⁽¹⁾	ZnMg	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	GC	600
35	304L	-	-	-	-	-	-	-	CM755008	-	-	-	-	-	-	-	-	-	-	-	304L	35
50	304L	-	-	CM925018	CM004068	-	-	-	-	-	-	-	-	-	CM348060	-	CM348050	-	-	-	304L	50
100	304L	-	-	CM925028	CM004078	CM003228	-	-	-	-	-	-	-	-	-	-	-	CM001113	-	-	304L	100
150	304L	-	-	CM925038	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	304L	150
200	304L	-	-	CM925048	CM004098	CM003248	-	-	-	-	-	-	-	-	-	-	-	-	-	-	304L	200
300	304L	-	-	-	CM004108	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	304L	300
400	304L	-	-	-	CM004208	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	304L	400
450	304L	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	304L	450
500	304L	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	304L	500
600	304L	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	304L	600
35	316L	-	-	-	-	-	-	-	CM755004	-	CM755104	-	CM430114	-	-	-	-	-	-	-	316L	35
50	316L	CM646014	-	CM925014	CM004064	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	50
100	316L	CM646024	-	CM925024	CM004074	CM003224	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	100
150	316L	CM646034	-	CM925034	-	CM003234	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	150
200	316L	CM646044	-	CM925044	CM004094	CM003244	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	200
300	316L	CM646054	-	-	CM004104	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	300
400	316L	CM646064	-	-	CM004204	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	400
450	316L	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	450
500	316L	CM646074	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	500
600	316L	CM646084	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	316L	600

(1) = Auf Anfrage

(1) = Auf Anfrage